

HI97720 · HI97719

Hardness Standard Method Portable Photometers

- Advanced LED optical system
 - Innovative optical design that utilizes a reference detector and focusing lens to eliminate errors from changes in the light source and from imperfections in the glass cuvette.
 - LEDs have a much higher luminous efficiency, providing more light while using less power. They also produce little heat, which could otherwise affect electronic stability.
- CAL Check™
 - Validate instrument performance at any time using CAL Check cuvettes made with NIST traceable standards. The CAL Check screen guides the user step-by-step through the validation process and user calibration.
- On-screen tutorial mode with animations
 - Guides users step-by-step through the measurement process
- Waterproof and floating IP67 case
- Unit of measure is displayed along with reading
- Built-in timer
 - Built-in reaction timer that ensures consistency between tests.
- Error messages on display
 - Alerts to problems including no cap, high zero, and standard too low
- GLP data
 - Displays the last calibration date.
- Auto logging
- Battery status indicator
- Auto-shut off

Significance of Use

Water, with exception to distilled water, contains dissolved salts (magnesium and calcium carbonates). The concentration of these salts determines the water hardness, which can be expressed in calcium carbonate or magnesium carbonate. The sum of these two represents the total hardness level. In addition, water hardness is also related to the phenomenon of pipe rusting in water heating and cooling systems, reverse osmosis, and demineralization plants.



| Specifications | HI97720 Ca Hardness | HI97719 Mg Hardness |
|---------------------------|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------|
| Measurement | Range | 0.00 to 2.70 mg/L (ppm) (as CaCO ₃) |
| | Resolution | 0.01 mg/L |
| | Accuracy @25°C (77°F) | ±0.11 mg/L ±5% of reading |
| Measurement System | Method | adaptation of the Standard Methods for the Examination of Water and Wastewater, 18th ed. Calmagite method |
| | Light Source | light emitting diode |
| | Bandpass filter | 525nm |
| | Bandpass filter bandwidth | 8 nm |
| | Bandpass filter wavelength accuracy | ±1.0 nm |
| | Light Detector | silicon photocell |
| Additional Specifications | Cuvette type | round 24.6 mm diameter (22 mm inside) |
| | Auto logging | 50 readings |
| | Display | 128 x 64 pixel B/W LCD with backlight |
| | Auto-off | after 15 minutes of inactivity (30 minutes before a READ measurement) |
| Battery type / Life | alkaline 1.5 V AA (3) / > 800 measurements (without backlight) | |
| Environment | 0 to 50°C (32 to 122°F); 0 to 100% RH, non-serviceable | |
| Dimensions | 142.5 x 102.5 x 50.5 mm (5.6 x 4.0 x 2.0") | |
| Weight | 380 g (13.4 oz.) | |

Ordering Information

HI97720 and **HI97719** are supplied with sample cuvettes (2), sample caps (2), plastic stoppers (2), 1.5V AA batteries (3), instrument quality certificate, and instruction manual. CAL Check standards and testing reagents sold separately

HI97720C and **HI97719C** includes photometer, CAL Check standards, sample cuvettes (2), sample caps (2), plastic stoppers (2), 1.5V AA batteries (3), 1 mL syringe with tip, cuvette wiping cloth, CAL Check standard certificate, instrument quality certificate, instruction manual, and rigid carrying case.

Reagents sold separately

Reagents and Standards

| | |
|---------|----------------------------------------------------------------------|
| HI97720 | HI97720-11 CAL Check standard cuvettes for calcium hardness |
| | HI93720-01 calcium hardness reagents for 100 tests |
| | HI93720-03 calcium hardness reagents for 300 tests |
| HI97719 | HI97719-11 CAL Check standard cuvettes for magnesium hardness |
| | HI93719-01 magnesium hardness reagents for 100 tests |
| | HI93719-03 magnesium hardness reagents for 300 tests |